

MILAN S.r.l. a socio unico


Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet

tasker® C275 – 2x1,50 mm²

Flexible Double Density Sheath Speaker Cable



CATEGORY **Flexible Speaker Cable (See Audio Catalogue)**

- A:** First Soft **PVC** sheath - available in different color.
Outer cable Ø: 8,00 (±0,10) mm.
- B:** Second Soft **PVC** Sheath with different density.
- C:** Core Insulation with a Third PVC Sheath, colored one Red and one Black.
Nom. Ø: 3,00 (±0,10) mm.
- D:** O.F.C. red copper formation 48x0,20 mm.
Nom. Cross section 2x1,50 mm².

MARKING **tasker® C275 2x1,50 – 16 AWG O.F.C. Speaker Cable Loudspeakers**
 Cable - Made In Italy

CUSTOM This product is also available in **L.S.Z.H.** polymer, **PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	16 Ω/Km ± 5%
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. D / 16.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione		