

HI-98501

Thermometer CheckTemp Stick

Checktemp® C Electronic Digital Thermometer

±0.3°C accuracy

CAL CHECK®

Ideal for spot checks

Fast and accurate results

If you ever wished that your temperature measurements could be made a little easier, the Checktemp® might just be what you're looking for! The Checktemp® offers high accuracy over a wider range without worrying about breakage or condensation.

The Checktemp® offers NO breakage, NO waste, NO injuries, NO difficulty in reading; not even a parallax error by taking a wrong measurement due to the angle of view!

Checktemp® is provided with HANNA's unique CAL CHECK™ function for accurate measurements every time: simply activate a switch and the instrument will simulate an ice bath of 0.0°C (32.0°F) signal that is displayed on the LCD within a range of ±0.3°C (±0.5°F).

The sharp-tip probe of the Checktemp® easily penetrates semisolid products, making routine controls simple and quick for both incoming and outgoing goods. Checktemp® is the ideal instrument for measuring temperature according to HACCP requirements.

Models with factory calibration certificate against NIST standards are also available.



Order Information:

HI 98501 (Checktemp®C) is supplied with penetration probe, protective cap, battery and instructions.

Specifications

Accuracy		±0.3°C (-20 to 90°C) ±0.5°C (outside)
Battery Type / Life		1 x 1.5V / approx. 3000 hours of continuous use
Dimensions		66 x 50 x 25 mm (2.6 x 2.0 x 1.0") - meter only
Environment		0 to 50°C (32 to 122°F); RH max 95%
Probe		fixed stainless steel 105 x dia 3 mm (4.1 x dia 0.1") (penetration)
Range		-50.0 to 150.0°C
Resolution		0.1°C
Weight		50 g (1.8 oz.) - meter only