



1. Material Specifications					
	100236	100238	100239	100237	100214
Colour	Black	Light Grey	Black	Grey	Black
Hardness	ShA 50±10	ShA 50±10	ShA 60±10	ShA 50±10	ShA 70±10
Flammability	-	-	UL94 V-0	-	-

- REACH & RoHS Compatible
- Metal Insert According to Drawing:  
"100420.pdf"
- 2. Elastomer ISO 3302-1: M3, X3
- 3. Protection Class IP 65
- 4. Supported Cable Diameters:
  - 5-7mm 4pcs
  - 8-12mm 4pcs
  - 10-14mm 12pcs
  - 14-20mm 4pcs
  - 20-26 1pc
- 5. Surface Finish VDI 3400 nr 14-35

SCALE <b>1:1</b>	VOLUME 119.2cm <sup>3</sup>	TOLERANCE ISO 3302-1 M3	MATERIAL <b>TPE</b>	PRODUCT NAME <b>MC 25</b>
REV	DESIGNER <b>J.Lehtonen</b>	DATE 23.5.2016	WEIGHT 119.2 g	CODE 100236, 100238, 100237, 100239, 100214
SIZE <b>A3</b>	APPROVED	DATE		DRAWING NUMBER <b>MC 25</b>



© Copyright by Trelleborg  
Proprietary data, all rights reserved