


E12492



Connection cable

VSTGN040ZDS0010L04STGP080--S



Application

Special feature	Screened cable
Design	Ethernet cable, D-coded
Application	cross-over patch cable; patch cable

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67; IP 20; (M12 plug / RJ45 plug)

Mechanical data

Weight	[g]	702.5
Materials		TPU / PA
Material nut		diecast zinc, nickel-plated

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug M12

Connector: 1 x M12, straight; Moulded body: PA; Locking: diecast zinc, nickel-plated; Tightening torque: 0.7...0.9 Nm



E12492




Connection cable

VSTGN040ZDS0010L04STGP080--S

Electrical connection

Cable: 10 m, PVC, green, \varnothing 6.5 mm, shielded; 2 x 2 x 0.38 mm²

Connection



Electrical connection - plug RJ45

Connector: 1 x RJ45, straight; Moulded body: TPU

