



ACRYLIC FIBRES ON REEL 50 M

Fibre optics



Product characteristics

acrylic fibres on a reel

50 m

Connection to fibre optic amplifiers type OBF

Environment

Ambient temperature [°C] -40...70

Mechanical data

Design for types OBF, OOF

Length [mm] 50000

Min. bending radius [mm] 30

Fiber arrangement



Fibre diameter [mm] 1

Outer diameter [mm] 2.2

Fibre optic PMMA; can be cut to length

Sheathing PE (polyethylene)

Weight [kg] 0.451

Remarks

Pack quantity [piece] 1