

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2059570671](#)

Status: **Active**

Overview: [Micro-Lock Plus Wire-to-Board Connector System](#)

Description: 1.25mm Pitch, Micro-Lock Plus PCB Header with Potting Capability, Single Row, Vertical, Surface Mount, Tin-Bismuth Plating, Positive Lock, 6 Circuits, Tape and Reel, Black

Documents:

3D Model	Application Specification AS-505565-001-001 (PDF)
Drawing (PDF)	Packaging Specification 2059579200-SPK-200 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification 2045320001-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	205957
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock Plus
UPC	191130032211

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	270.200/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Tape
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[205957](#) Series

Mates With

[Micro-Lock Plus Receptacle Housing](#)
[204532](#)

Electrical

Current - Maximum per Contact

3.6A

Voltage - Maximum

50V AC (RMS)/DC

Material Info**Reference - Drawing Numbers**

Application Specification

AS-505565-001-001

Packaging Specification

2059579200-SPK-200

Product Specification

2045320001-PS-000

Sales Drawing

2059573000-SD-000

This document was generated on 03/11/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION