


TECHNICAL SPECIFICATION

MODEL NO

A-1430WPUK

Wall Plate Audio Amplifier
with CSR Bluetooth v4.2



Power Supply

SPECIFICATIONS :

- ◆ Audio Inputs : Bluetooth Receiver or stereo audio line level
- ◆ Bluetooth Version : Bluetooth v4.2 compliant with aptX
- ◆ Bluetooth Receive Distance:50 Meters (open space)
- ◆ Power Amplifier Type:Stereo Class-D
- ◆ Output power : 24W(rms) per channel (@ RL=4 ohm)
- ◆ THD+N : 0.1 % (@ RL=4 ohm, f = 1 kHz)
- ◆ Minimum Load Resistance : 4 ohm
- ◆ Includes Speaker Protection circuit.
- ◆ Power Source : 24 VDC/3A
- ◆ 3 min link-lost timeout function. Bluetooth automatically switch to pairing state if reconnecting fail.
- ◆ Audio priority : BT > Line In.

Bluetooth Blue LED Status :

LED state	Statement
Blue led on : 1 sec , off : 2 sec , repeat	All profiles are standby but not connected with any Bluetooth device yet.
Blue led flash every 2 sec	A2DP or HFP is connected.
Blue led flash twice every 2 sec	On A2DP streaming state.
Blue led On: 150ms, Off: 150ms repeat	Enter pairing mode.