#### **KNIPEX** Quality – Made in Germany



### **Product information**

# 95 36 280

## Cable Cutter

(ratchet action)

IEC 60900 DIN EN 60900



#### • Suitable for aluminium sector cable up to 4 x 150 mm<sup>2</sup>

- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire, wire ropes and fine-stranded (highly flexible) conductors
- Precision-ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principleLittle handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design can be used even in confined areas
- Pinch guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened

#### You You

Gonoral

General	
Article No.	95 36 280
EAN	4003773026891
Pliers	black lacquered
Handles	insulated with multi-component grips, VDE-tested
Weight	835 g
Dimensions	280 x 135 x 28 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple- stranded	380 mm <sup>2</sup>
Cutting capacity copper cable, multiple- stranded	Ø 52 mm
MCM	750
VDE tested	yes

technical change and errors excepted





Ratchet principle and two-stage ratchet drive for easier cutting