

Elastic mounting plates

EFFBE

Application:

For non-slip anchor-free erection of machines and apparatus for which there are no means of fixing for levelling elements (no. 26400). An angled stay can be cut off for arranging in rows.

Execution:

- Elastomer body 802 C (CR 80 Shore A)
- Resistant to oil and ageing
- Non-slip

Advantage:

- No anchor points required



Art. no.	26402 010
Brand	EFFBE
Manufacturer Part Number	FB620042 14
Model	EPA 7
Supporting plate length	75 mm
Supporting plate width	75 mm
Supporting plate height	13 mm
Load-carrying capacity	750 kg
Gross Weight	0.102 kg
Product Group	265