

Workbench with manual height adjustment

Solid beechwood 1500 mm, height-adjustable via crank handle

Application:

For standing activities.

Execution:

- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, central horizontal strut, with level compensation on all four feet
- Continuous height adjustment from approx. 740-1040 mm via hand crank (removable)
- Bevel gears with hardened steel gear wheels
- Gear housing made of fibreglass-reinforced plastic
- Fully assembled incl. crank handle

Advantage:

- The workbench can quickly and easily be adjusted to the desired working height
- For perfect ergonomics in the workplace
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50185 002
Worktop width	1500 mm
Levelling	Yes
Worktop height	50 mm
Adjustable in height	Yes
Material of frame	Steel plate
Worktop depth	700 mm
Max. height adjustment	1040 mm
Min. height adjustment	740 mm
Surface	Powder-coated
Load-carrying capacity	800 kg
Dynamic load-carrying capacity	200 kg
Type	Height adjustable via hand crank
Material of worktop	Solid beech
Product Group	5BC

EAN

4053625048847