

Pneumatic blow-out and liquid gun MultiFLOW

Steel nipple, 1/4 inch female thread



Application:

For cleaning work using compressed air, coolant or non-explosive water-based liquids.

Version:

- Zinc-plated steel adapter, 1/4" female thread
- Precisely adjustable flow rate regulation
- Satisfies OSHA requirements
- Flat or concentrated jet with adjustable jet nozzle



Art. no.	75103 030
Type	Steel nipple, 1/4 inch female thread
Min./max. flow capacity	5-25 l/min
Min. air consumption	200 l/min
Max. air consumption	1200 l/min
Min./max. air consumption	200-1200 l/min
Max. operating pressure	16 bar
Burst pressure	64 bar
Connection thread	R 1/4 inch
Min./max. sound-pressure-level	79-101 dB
Min./max. temperature conditions	-20 to +60 °C
Weight	0.205 kg

EAN-Code

7391390264053