

Manual pick-up magnet

Permanently high magnetic force

Application:

For the safe manual transport of sheet metal and steel parts.

Version:

- **Ref. no. 010** for thin sheets and small pieces.
- **Ref. no. 020** particularly for medium- and large-sized sheets (most popular model).
- **Ref. no. 030** for thick plates, heavily scaled plates, heavy workpieces.

Advantage:

- Entirely maintenance-free
- Permanently high magnetic force
- No magnetisation of workpieces

Art. no.	77350 020
Load-carrying capacity	170 kg
Suitable for min./max. sheet metal thickness	1-4 mm
Surface area length	140 mm
Surface area width	116 mm

