

# Power Strip

LED, 6xT13, 3 m, Type 12/Protective contact



With 10 A protector (thermo fuse)

Reconnectable with internal supply terminals

Impact resistant and halogen-free case

Flexible positioning in racks, rear walls and housing frame

Fastening clips included

In accordance with the Swiss Ordinance on Low-Voltage Electrical Equipment (CVEO), approved by the Swiss Federal Inspectorate for Heavy Current Installations


## SPECIFICATION:

No. of USB	2-port (5 VDC/2.1 A)
No. of sockets	6
Socket type	T13
Colour	black
Cable length	3 m
Plug type	Type 12/Protective contact
Rated output	2.5 kW
Load capacity	10 A/230 VAC
Dimensions L x W x H	433 x 44.4 x 44.45 mm
Socket arrangement	Lengthwise
Connecting cable	H05VV-F. 3G 1 mm <sup>2</sup>
Material	Aluminium/Polypropylene
Assembly type	19" System
Mounting	Horizontal/Vertical






**Art. Nr.**

**RND 465-00214**



Copyright 2016 - RND

RoHS Compliant



With Terminal Block inside

Earthing Way

Screw / Nut / Ring

DRAWING TYPE CATIA (NO FEMOTION REQUIRED)	unit=mm	
	TECHNICAL STANDARD 2 HD RUSTINESS 3 HD FLAW ON THE SURFACE	
	FILLET	R0.5
	ANGLE	±0.5°
FIRST ANGLE		
SCALE 1:3		

RND 465-00214

Aluminium

Black Anodized

Housing



DATE 13-12-2016

Revisions		
Rev	Description	Date

<b>Basic Series</b>	<b>OUTPUT</b>	<b>OPERATING TEMPERATURE</b>
	(6) Black Sev type 13 (2) USB 5V DC Total 2.1A Max	0° to 60°C
<b>INPUT</b>	<b>BRANCH CIRCUITS</b>	<b>MOUNTING ACCESSORIES</b>
250VAC 10A 50HZ T12 plug 3M H05VV-F3G1.0mm <sup>2</sup> Power lead	(1) 10A Sangmao	(2) 42 Bracket

8

7

6

5

4

3

2

1