




Dimensions



Model Number

V15-G-2M-PUR-V15-G
 Connecting cable, M12 to M12, PUR cable 5-pin


Features

- Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- Gold plated contacts
- Degree of protection IP67 / IP68 / IP69K
- Halogen-free
- Suitable for 2-, 3- and 4-wire technology

Technical data

General specifications		
Number of pins		5
Electrical specifications		
Operating voltage	U _B	max. 60 V DC
Test voltage		> 1500 V _{eff} AC
Operating current	I _B	max. 4 A
Volume resistance		< 5 mΩ
Ambient conditions		
Ambient temperature		-25 ... 100 °C (-13 ... 212 °F) for temperatures over 80 °C (176 °F) reduced elongation at tear
Pollution Degree		3
Mechanical specifications		
Contact elements		spring-loaded contact socket
Pin diameter		1 mm
Degree of protection		IP67 / IP68 / IP69k
Material		
Contacts		CuSn / Au
Contact surface		Au
Body		TPU, black
Cable		PUR
Slotted nut		Diecast zinc
Sleeve connector		Diecast zinc
Core insulation		PP
Cable		fine-strand, flexible
Sheath diameter		Ø4.8 mm
Bending radius		> 10 x cable diameter, moving
Color		grey
Cores		5 x 0.34 mm ²
Conductor construction		19 x 0.15 mm Ø
Length	L	2 m
Flammability		
Contact material		94 V-2
Housing		94 V-2

Electrical connection



Release date: 2015-01-08 15:27 Date of issue: 2015-01-08 200814_eng.xml