



Specifications

Lamp Base Type LED Colour Dimmable Luminous Flux Power Rating Voltage Rating Life Span On/Off Temperature CRI Beam Angle Equivalent Power Efficiency Rating Power/1000h

Dimension($L \times D$)

- : E27
- : Daylight White
- : Dimmable
- : 400lm
- : 5W
- : 220V AC to 240V AC, 50/60Hz
- : 25000h
- :≥15000
- : 6500K
- : ≥80
- : 180°
- : 35W
- : A+
- : 5kwh/1000h
- : 108.5mm×60mm

Part Number Table

Description	Part Number
LED GLS Bulb, E27, Daylight White, 6500K, Step Dimmable, 180°	PEL00242

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

