

## Product information

# 26 22 200 T

## Snipe Nose Side Cutting Pliers (Stork Beak Pliers)

DIN ISO 5745

- Elastic tips: dimensionally stable even when twisted
- Pliers with tether attachment point for mounting a fall protection system
- Distortion-tolerant, elastic precision tips
- Half-round, long, tapered jaws
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



| General         |   |
|-----------------|---|
| Article No.     | 26 22 200 T   |
| EAN             | 4003773080008   |
| Pliers          | black atramentized  |
| Head            | polished  |
| Handles         | with multi-component grips, with integrated tether attachment point for a tool tether |
| Weight          | 202 g   |
| Dimensions      | 200 x 57 x 27 mm  |
| Standard        | DIN ISO 5745  |
| REACH compliant | does not contain SVHC   |
| RoHS compliant  | not applicable  |

| Technical details                              |          |
|--|----------|
| Cutting capacities medium hard wire (diameter) | Ø 3.2 mm |
| Cutting capacities hard wire (diameter)        | Ø 2.2 mm |
| Jaw thickness (joint) (T1)                     | 9.5 mm   |
| Tips width (W4)                                | 3.0 mm   |
| Tips thickness (T2)                            | 2.5 mm   |
| Gripping surface length (L4)                   | 23.0 mm  |
| Jaw length (L3)                                | 73.0 mm  |
| Head width (W3)                                | 18 mm    |

## Technical details



*technical change and errors excepted*



