


ART.: 3105560

WL390 opal



Art.: 3105560, LED-Wall and ceiling mounted luminaire 3K/4K 29/38W static opal-white diffuser, Wall and ceiling mounted LED luminaire for indoors, comprising: Technopolymer housing (WL210/WL390) / Die-cast aluminium housing, powder-coated (WL260) / Light orienting technopolymer optic for a homogenous light distribution over the entire area of the cover / Direct light distribution / Colour rendering index Ra > 80 / LED lifetime 50.000 h at 80% luminous flux (L80B10) / Colour tolerance according to MacAdam ≤ 3 SDCM / Light colour can be selected between 3000K and 4000K / Two power levels can be set via a switch / Complete with electric converter / Through wiring / AC/DC-ready / Overall efficacy > 100 lm/W

Connected load	38 W
Luminous flux	4020 lm
Efficiency	106 lm/W
Colour temperature	4000K
Colour rendering (CRI)	80
IP class	20
Nominal voltage	220 – 240 V
Colour	GR-94
UGR	18,9

