

Die, HSS MF right, pre-slotted and 1.75 thread chamfer

for universal use up to 700 N/mm²

ORION[®]

Application:

For cutting fine metric threads externally in the material groups of steel and non-ferrous metals up to a strength of 700 N/mm².

Execution:

- right die, tol. 6 g with spiral point, pre-slotted and 1.75 pitch

Advantage:

- standard geometry with excellent price/performance ratio



Art. no.	13445 246
Brand	ORION
Manufacturer Part Number	13445246
Thread type	Metric fine thread
Cutting material	HSS
Tolerance of dies	6 g
Thread type x nominal diameter	MF24
Pitch	2 mm
Outer diameter	55 mm
Height	16 mm
Cutting direction	Right-hand cutting
Gross Weight	0.195 kg
Product Group	1DC

EAN

4039247073757