

cabinet workbench series V 1500 with knee space

Universal coating 1500 mm, 2 drawers with full extension



Application:

for seated working

Execution:

- Solidly welded steel sheet construction
- Base made of square-section steel tube 45 x 45 x 2 mm, with level compensation
- 2 drawers with 100% full extension on the left, 1 x front height 180 mm, 1 x front height 360 mm, recessed shelf on the right



Art. no.	50201 555
Number of drawers	2 PCS
Working height	850 mm
Worktop width	1500 mm
Pullout type	Full extension
Worktop height	50 mm
Colour of front	Gentian blue RAL 50 10
Worktop depth	700 mm
Cabinet colour	Light grey RAL 7035
Drawer surface	0.27 m ²
With single pull-out safety brake	Yes
Levelling	Yes
Lock type	DOM® locking system
Drawer front height	1 x 180 mm, 1 x 360 mm
Drawer width (inner dimension)	500 mm
Surface	Powder-coated
Drawer width (inner dimension) x drawer depth (inner dimension)	500 x 540 mm
Load-carrying capacity	1500 kg
Drawer depth (inner dimension)	540 mm
Load-carrying capacity per drawer	100 kg
Material of worktop	Universal covering
Central locking	Yes
Product Group	Prod. Gr. 502

EAN

4014641009526