

Cabinet trolley with 5 load areas

Grid on 3 sides and door, total carrying capacity 750 kg

Application:

For the safe transport and storage of materials and goods.

Version:

- Angle steel structure completely welded with tubular push handle
- Front walls 1 longitudinal wall and roof made from wire grid (40 x 40 x 4 mm)
- With double winged door made of angle steel with welded in wire grid
- Double-folding door with vertical locking rod with swivelling lever and cylinder lock
- 1 firm and 4 loose bottoms
- Made of rigid sandwich plates
- Distance of shelf light 280 mm
- 2 fixed castors and 2 swivel castors, including TOTALSTOP
- With shootbolt rod

Advantage:

- Convenient Total Stop included

Delivery:

Assembled



Art. no.	50268 782
Material of loading surface	Wood
Load-carrying capacity	750 kg
Load-carrying capacity of loading surfaces	90 kg
Number of loading surfaces	5 PCS
Loading surface size	1000 x 680 mm
Loading-surface width	680 mm
Loading-surface height	292 mm, 582 mm, 882 mm, 1182 mm, 1482 mm
Loading surface length	1000 mm
Length	1170 mm
Width	745 mm
Height	1792 mm
Number of panels	4 PCS
Material of wall	Wire mesh
Number of fixed rollers	2 PCS
Length x width x height	1170 x 745 x 1792 mm
Number of steering rollers	2 PCS
With wheel lock	Totalstop
Wheel width	40 mm
Wheel diameter	200 mm
Material of wheel	TPE
Lock type	Cylinder lock
Colour	Brilliant blue RAL 5007
Surface	Powder-coated
EN standard	1757-3
Colour of loading area	Beech
Design	With mesh panels on three sides and doors

EAN-Code

4017976013176