

Cut protective gloves

Model: HYFLEX 11-738

Ansell

Application:

For assembly work involving sharp-edged parts

Execution:

- Excellent flexibility and fit
- INTERCEPT yarn for excellent comfort and dexterity
- high breathability
- Additional nitrile reinforcement in the crook of the thumb
- Seamless processing
- With knitted cuff



| | |
|--|---|
| Art. no. | 55523 319 |
| Brand | ANSELL |
| Manufacturer Part Number | 11738090 |
| Category | II |
| Cut protection | Yes |
| EN standard | 388 |
| ISO | 21420 |
| Model | HYFLEX 11-738 |
| Backing material | INTERCEPT®-technology cotton, Nylon with spandex fiber, Glass fiber |
| Gauge | 13 |
| Coating | Polyurethane, Nitrile |
| Silicone-free | Yes |
| Approval mark | OEKO-TEX Standard 100 |
| Size | 9 |
| Abrasion resistance | 4 |
| Cut resistance according to EN 388 | X |
| Tearing strength | 4 |
| Puncture resistance | 2 |
| Cut resistance according to ISO 13997 | C |
| Gross Weight | 0.083 kg |
| Product Group | 5SB |

EAN

20076490478609