Full HD Outdoor Wi-Fi Spotlight Camera



mydlink

OO LUMEN

Your Home, Only Smarter

The mydlink[™] Full HD Outdoor Wi-Fi Spotlight Camera boasts a wide-angle lens accompanied by a 400-lumen spotlight and colour night vision, easily capturing your entire outdoor area in high-quality 1080p. It has an IP65 rating with a wide operating temperature between -25°C and 45°C, which means it can withstand outdoor weather environments and protected against rain, moisture and dust.

Integrated AI-Based Motion and Sound Detection

Al-based motion and sound detection processes information in real-time, intelligently distinguishing between human and non-human moving objects, as well as the sound of breaking glass. As the intelligence integrated within the camera, detection is faster, requires less bandwidth and subscription free. Passive Infrared (PIR) sensor further enhances the accuracy of motion detection, dramatically reduces false alarms.

Instant Notification with Video Recording

Built-in motion and sound detection automatically alerts you and starts recording if movement or sound is detected. Built-in 100 dB siren can also be used to scare off intruders or alert you to a detection. The integrated microSD card slot and optional free/paid mydlink cloud subscription allows you to store videos and snapshots locally or remotely to your personal cloud storage. You can even playback and download recorded videos from anywhere in the world on your smartphone or tablet. With the built-in microphone and speaker, you can talk to family members while viewing them on your screen.

works with alexa

D-Link®



Google Assistant

Product Highlights

400 Lumen Spotlight



Built-in LEDs cast a bright light over the camera's view

Colour Night Vision

See and record full color video up to 7 meters in low-light conditions

Person Detection




Delivers smarter, more relevant

Features

- True Full-HD quality with 150° wide angle views (1080p at 30 frames per second)
- Colour night vision with bright 400-lumen spotlight illumination
- Passive Infrared (PIR) sensor for highly accurate motion detection that reduces false alarms, even in complete darkness
- Al-based motion and sound detection to detect human objects and sound of breaking or shattering glass
- Built-in 100 dB siren to scare off intruders or alert you to a detection
- Built-in microphone and speaker for twoway communication
- Works with, Amazon Alexa and the Google Assistant¹
- Rich Notifications let you take action right from your lock screen
- Record videos² to a microSD card³, your phone, or the cloud
- Connects to your home's existing Wi-Fi
- Compatible with NVR and VMS through ONVIF Profile S



Product Image



Technical Specifications

Camera		
Hardware Profile	 1/2.9" Progressive CMOS sensor 7 m (23 ft) IR illumination distance Built-in Infrared-Cut Removable (ICR) Filter module Fixed length 2.7 mm Aperture F2.0 	 Angle of view (16:9): Horizontal: 123.8° Vertical: 65.4° Diagonal: 150° Built-in microphone and speaker
Image Features	 Configurable image size Person detection Motion detection (PIR sensor, 1 zone) 	Invert imageColour night vision
Video Compression	H.264 format compression	
Video Resolution	• Max. resolution: 1080p (1920 x 1080) at up to 30 fps	
Audio Support	• MPEG-2 AAC LC	
Network		
Connectivity	 802.11n/g wireless with the latest industry-standard 128- bit wireless encryption Wi-Fi operates on 2.4 GHz band 	 microSD card slot³ Supports up to 256 GB capacity Bluetooth Low Energy 4.0
Network Protocols	 IPv4, IPv6 DHCP/DHCPv6 Client Bonjour (mDNS and DNS-SD) ONVIF Profile S 	• RTSP • SRTP • RTP/SRTP • HTTPS



DCS-8627LH Full HD Outdoor Wi-Fi Spotlight Camera

System Integration			
Event Management	 Motion detection Person detection Sound detection Cloud recording SD card recording Day & Night mode 	 Glass Breaking sound detection Push Notifications with a snapshot when the device detects motion/people/sound Push Notifications with quick action buttons: Call up to 2 designated contact numbers Live view button 	
Device Management	• mydlink app	• mydlink Portal (for live view only)	
Physical			
Environment	For indoor and outdoor useWall or pole mountable	IP65 weatherproof rating	
Weight	• 237 g		
Power Adaptor	 Input: 100 to 240 V AC, 50/60 Hz Output: 12 V DC 1.0 A 	• Cable length 3 m (9.84 ft)	
Power Consumption	• Maximum 8 W ± 5%		
Temperature	• Operating: -25 to 45 °C	• Storage: -20 to 70 °C	
Humidity	Operating: 20% to 90% non-condensing	Storage: 5% to 90% non-condensing	
Certifications	• CE • LVD • RCM	 FCC Class B IC NCC/BSMI 	
Dimensions (L x W x H)	• 126 x 84 x 60 mm (5.0 x 3.3 x 2.3 in)		

¹ Alexa service and the Google Assistant may not be available in all regions.² Use of audio or video equipment for recording the image or audio of a person without their knowledge and consent is prohibited in certain states or jurisdictions. The end-user assumes all liability for compliance with applicable state, local and federal laws.³ microSD card not included. Supports capacity up to 256 GB.



For more information: www.dlink.com



D-Link European Headquarters. D-Link (Europe) Ltd., First Floor, Artemis Building, Odyssey Business Park, West End Road, South Ruislip HA4 6QE, United Kingdom. Specifications are subject to change without notice. D-Link is a registered trademark of D-Link Corporation and its overseas subsidiaries. All other trademarks belong to their respective owners. ©2020 D-Link Corporation. All rights reserved. E&OE. Updated April 2020