




USB 2.0, Type A Male Connector modular

Item No. 2001C198



mm±0.2



PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND



Screwdriver Included

Material:
 Housing: PP
 Insulator: LCP
 Connector shell: SPCC with plated Ni 40µ min.
 Contact: Brass with plated Au1µ
 Technical:
 Voltage rating: 5V max.
 Current rating: 2A max.
 Contact resistance: 30mΩ max.
 Insulation resistance: 1000MΩ min.
 Dielectric withstanding voltage: 500V/AC(R.M.S)
 Operation temperature: -20 ~85°C