












ESD ELECTRONIC PLIERS CLASSICLINE

The pliers in the CLASSICline series are characterised by their high-gloss electropolished surface, which is very resistant to corrosion, without friction and microcracks, extremely smooth and free of particles. The heads are ideal for working on small components.

The pliers sit perfectly in the hand thanks to their two-component protective covering, which is ergonomically shaped, dissipative and features an individually adjustable double leaf spring. The smooth box joint guarantees a long service if cared for properly.

The pliers have been tested with great results in accordance with DIN EN 61340-5-1, 61340-2-1 and 61340-2-3, as well as for work in ESD protected areas.



The following types are available, specifications in mm:

Art.-No.	Short description	Type	Flush	○	⊘	●	⊕	Head width	Cutting length	Total length	Weight in g
▶ CUTTING PLIERS											
3-601-15	ESD side cutters	-	Semi flush	1.5	1.2	0.4	-	11	13	115	65
3-602-15	ESD side cutters	-	Flush	1.5	1.2	-	-	11	13	115	65
3-603-15	ESD side cutters	-	Semi flush	1.5	1.2	0.3	-	11	13	115	65
3-604-15	ESD side cutters	-	Flush	1.5	1.2	-	-	11	13	115	65
3-606-15	ESD side cutters	-	Flush	1.0	0.8	-	-	10.5	6	120	55
3-625-15	ESD oblique top cutters	-	Flush	1.5	1.2	-	-	11	11	120	90
3-627-15	ESD top cutters	-	Flush	1.5	1.2	-	-	11	11	120	90
▶ HOLDING PLIERS											
										jaw length	
3-631-15	ESD round nose pliers	not serrated jaws	-	-	-	-	-	10	20	120	55
3-632-15	ESD flat nose pliers	not serrated jaws	-	-	-	-	-	9	18.5	120	55
3-633-15	ESD snipe nose pliers	not serrated jaws	-	-	-	-	-	9.5	17.5	120	55
3-634-15	ESD snipe nose pliers	not serrated jaws	-	-	-	-	-	9.5	22.5	120	55

p. 60

more VARIO sets
with pliers▶ **3-650 V****ESD pliers set CLASSICline VARIO 5 pcs**

150 x 190 x 80 mm

Weight: 750 g

Art.-No.	Content
5-090-0	ESD tool holder VARIO 8 slots
3-601-15	ESD side cutters CLASSICline semi flush 115 mm
3-631-15	ESD round nose pliers CLASSICline not serrated jaws 120 mm
3-632-15	ESD flat nose pliers CLASSICline not serrated jaws 120 mm
3-633-15	ESD snipe nose pliers CLASSICline not serrated jaws 120 mm
3-634-15	ESD snipe nose pliers CLASSICline not serrated jaws 120 mm



3-650 V

▶ **3-960 VC****ESD tool kit CLASSICline VARIO 6 pcs**

150 x 180 x 80 mm

Weight: 700 g

Art.-No.	Content
5-090-0	ESD tool holder VARIO 8 slots
3-601-15	ESD side cutters CLASSICline semi flush 115 mm
3-606-15	ESD side cutters CLASSICline flush 120 mm
3-632-15	ESD flat nose pliers CLASSICline not serrated jaws 120 mm
3-633-15	ESD snipe nose pliers CLASSICline not serrated jaws 120 mm
5-078-13	ESD SMD universal tweezers 130mm form PSF stainless steel dissipative
5-055-13	ESD SMD tweezers 120mm form 7a stainless steel angle 40° dissipative



3-960 VC

▶ **3-960 C****ESD pliers set CLASSICline 4 pcs**

320 x 150 x 20 mm

Weight: 380 g

Art.-No.	Content
3-960-0	ESD dissipative bag 4 empty compartments
3-601-15	ESD side cutters CLASSICline semi flush 115 mm
3-606-15	ESD side cutters CLASSICline flush 120 mm
3-632-15	ESD flat nose pliers CLASSICline not serrated jaws 120 mm
3-633-15	ESD snipe nose pliers CLASSICline not serrated jaws 120 mm



3-960 C