






# 69001-712 STECKVERBINDER F, EN 60603, DIN 41612, FEDERLEISTE, 48 KONTAKTE, LÖTAUGEN, 9,5 MM



## KEY FEATURES

Anforderungsstufe 2 nach EN 60603-2, (DIN 41642)

Codierung separat bestellen

## PRODUKTMERKMALE

Produkttyp: Steckverbinder

Typ: Federleiste

Passend zu: Front-Platten

Anzahl Kontakte: 48

Kontaktfläche: Hartvergoldet

Anschlussraster 5,08 mm

Kriechstrecken Kontakt-Kontakt [mm]: 3 mm

Luftstrecke Kontakt-Kontakt [mm]: 1,6 mm

Max. Strom bei 20°C: 6-A

Max. Widerstand: 20 mΩ

Max. Steck- und Ziehkräfte [N]: 75 N

Prüfspannung Ueff Kontakt-Kontakt [kV]: 1,55 kV

Prüfspannung Ueff Kontakt-Masse [kV]: 2,5 kV

Reihenzuordnung: Z; B; D

## ZUSÄTZLICHE PRODUKTDDETAILS

---

DIN-Steckverbinder/-Buchse Bauform F. Anforderungsklasse 2 nach EN 60603-2 (DIN 41642).

## ZERTIFIZIERUNGEN

---

**EAC**



### **Nordamerika**

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### **Europa**

Straubenhardt, Deutschland

+49.7082.794.0

Betschdorf, Frankreich

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### **Asia**

Shanghai, China

+86.21.2412.6943

Qingdao, Volksrepublik

China

+86.532.8771.6101

Singapur

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### **Middle East & India**

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, Indien

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
**nVent.com** **CADDY** **ERICO** **HOFFMAN** **RAYCHEM** **SCHROFF** **TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.