

1 2 3 4 5 6 7 8

A

A



B

B

MATERIAL


Insulator : PBT+30% Glass fiber
Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
Insulation Resistance : 100000MΩMin. at DC 500V
Contact Resistance : 20mΩMax. at DC 100mA
Dielectric Voltage : 750V AC for one minute



C

C



D

D



E

E

F

F

G

G

RoHS Compliant		HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准 HELEN		TOLERANCE 零件公差 0 ± 0.30 .00 ± 0.20 ANG. ± 3°	PART NAME 品名 2.54mm MINI JUMPER 2P H:6.5mm CLOSE COVER ROHS LOW-LEAD
DWG. 製圖 ABBY	SCALE 比例 參考	UNIT 單位 MM	SIZE. 紙張尺寸 A4
DATE 制表日 2011/03/23	PAGE 張數 1 OF 1	REV. 版本 A	PART NO. 料號 C2700-02ABXX00R

H

H

1 2 3 4 5 6 7 8