

# Stranded Wires

Stranded wire Copper unshielded



## FEATURES:

Class 5 flexible copper conductor

Fixed temperature rating -30°C to +70°C

For use in the switch control, relay and instrumentation panels, as internal connectors, motor starters and controllers

## SPECIFICATION:

Wire Code	H05V-K
Cable type	Stranded
Conductor	Copper
Conductor insulation	PVC
Original packaging	100 m
Rated voltage	300/500 V

## PRODUCT RANGE:

Art. no.	Colour	Cross-section
RND 475-00084	black	0.50 mm <sup>2</sup>
RND 475-00085	blue	0.50 mm <sup>2</sup>
RND 475-00086	brown	0.50 mm <sup>2</sup>
RND 475-00087	green/yellow	0.50 mm <sup>2</sup>
RND 475-00088	grey	0.50 mm <sup>2</sup>
RND 475-00089	red	0.50 mm <sup>2</sup>
RND 475-00090	white	0.50 mm <sup>2</sup>
RND 475-00091	yellow	0.50 mm <sup>2</sup>
RND 475-00092	orange	0.50 mm <sup>2</sup>
RND 475-00093	pink	0.50 mm <sup>2</sup>
RND 475-00094	violet	0.50 mm <sup>2</sup>
RND 475-00095	green	0.50 mm <sup>2</sup>
RND 475-00096	black	0.75 mm <sup>2</sup>
RND 475-00097	blue	0.75 mm <sup>2</sup>
RND 475-00098	brown	0.75 mm <sup>2</sup>
RND 475-00099	green/yellow	0.75 mm <sup>2</sup>
RND 475-00100	grey	0.75 mm <sup>2</sup>
RND 475-00101	red	0.75 mm <sup>2</sup>
RND 475-00102	white	0.75 mm <sup>2</sup>

<b>Art. no.</b>	<b>Colour</b>	<b>Cross-section</b>
RND 475-00103	yellow	0.75 mm <sup>2</sup>
RND 475-00104	orange	0.75 mm <sup>2</sup>
RND 475-00105	pink	0.75 mm <sup>2</sup>
RND 475-00106	violet	0.75 mm <sup>2</sup>
RND 475-00107	green	0.75 mm <sup>2</sup>
RND 475-00108	black	1.00 mm <sup>2</sup>
RND 475-00109	blue	1.00 mm <sup>2</sup>
RND 475-00110	brown	1.00 mm <sup>2</sup>
RND 475-00111	green/yellow	1.00 mm <sup>2</sup>
RND 475-00112	grey	1.00 mm <sup>2</sup>
RND 475-00113	red	1.00 mm <sup>2</sup>
RND 475-00114	white	1.00 mm <sup>2</sup>
RND 475-00115	yellow	1.00 mm <sup>2</sup>
RND 475-00116	orange	1.00 mm <sup>2</sup>
RND 475-00117	pink	1.00 mm <sup>2</sup>
RND 475-00118	violet	1.00 mm <sup>2</sup>
RND 475-00119	green	1.00 mm <sup>2</sup>