


# 24566-429 EUROPACPRO SIDE PANEL FOR STAINLESS STEEL GASKET, TYPE H, HEAVY, 6 U, 295 MM





### **KEY FEATURES**

For high mechanical demands, 19" bracket, tox-cold welded, Al, 2-mm, clear passivated, front anodized

Versions for EMC sealing (stainless steel or textile)

# **PRODUCT ATTRIBUTES**

Product Type: Side Panel

Product Family: EuropacPRO

Type: Type H

Rack Height: 6 U

Package Quantity: 2

Depth: 295 mm

# ADDITIONAL PRODUCT DETAILS

Side Panel, Type H, without handle holes, tox welded to the 19" bracket for stainless steel gasket.

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

9 U version available on request.



#### North America

All locations +1.763.422.2661 Chat with us: schroff.nyent.com

#### Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us:

schroff.nvent.com

nVent.com

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

#### Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER