


Synergy 21 LED LoRa (433MHz) Poolleuchte 27W RGB+CCT *Milight/Miboxer*



kwh/1000h:	27,00
Lumen:	2276
Watt:	27,0
Nennlebensdauer:	35000 Std.
Schaltzyklen:	50000
Opt. Umgebungstemp.:	25 °C



Product Name: 27W RGB+CCT Wall-mounted Underwater Light (LoRa 433MHz)
Model No.: UW02
Power: 27W
Input Voltage: AC12V / DC12~24V

Energieeffizienzklasse: A
kWh/1000h: 29,7
Working Temperature: -20~45?
RF: 433MHz
Modulation Method: LoRa spread spectrum
Control distance: 50m (Lamps into 0.5m underwater)
Color temperature: 2700K~6500K
Luminous Flux: 2000LM
Light Efficiency: 75LM/W
CRI: >80
Lifespan: 50000h
Beam Angle: 160°
IP Rate: IP68
Housing Material: 316 Stainless Steel+PC



Energieeffizienzklasse: A
kWh/1000h: 29,7


Merkmale

Merkmale	Wert
Abstrahlwinkel:	160
CC oder CV:	CV
Dimmbar:	Ja
EPREL_ANTI_GLARE_SHIELD:	false
EPREL_BEAM_ANGLE:	160
EPREL_BEAM_ANGLE_CORRESPONDENCE:	SPHERE_360
EPREL_CAP_TYPE:	Others
EPREL_CHROMATICITY_COORD_X:	0.311
EPREL_CHROMATICITY_COORD_Y:	0.329
EPREL_CLAIM_EQUIVALENT_POWER:	false
EPREL_COLOUR_RENDERING_INDEX:	80
EPREL_COLOUR_TUNEABLE_LIGHT_SOURCE:	false
EPREL_CONNECTED_LIGHT_SOURCE:	true
EPREL_CORRELATED_COLOUR_TEMP:	2700,6500
EPREL_CORRELATED_COLOUR_TEMP_TYPE:	RANGE
EPREL_DIMENSION_DEPTH:	100
EPREL_DIMENSION_HEIGHT:	300
EPREL_DIMENSION_WIDTH:	300
EPREL_DIMMABLE:	YES
EPREL_DIRECTIONAL:	NDLS
EPREL_ENERGY_CLASS:	F
EPREL_ENERGY_CONS_ON_MODE:	27
EPREL_ENVELOPE:	NON_CLEAR
EPREL_EQUIVALENT_POWER:	Not applicable
EPREL_FLICKER_METRIC:	0.1
EPREL_HIGH_LUMINANCE_LIGHT_SOURCE:	false
EPREL_HIGH_LUNINANCE_LIGHT_SOURCE:	false
EPREL_LIGHTING_TECHNOLOGY:	LED
EPREL_LUMEN_MAINTENANCE_FACTOR:	0.55


Merkmal	Wert
EPREL_LUMINOUS_FLUX:	2276
EPREL_MAINS:	NMLS
EPREL_MAX_COLOUR_RENDERING_INDEX:	86
EPREL_MIN_COLOUR_RENDERING_INDEX:	80
EPREL_ON_MARKET_END_DATE:	47849
EPREL_ON_MARKET_START_DATE:	43831
EPREL_POWER_ON_MODE:	22.9
EPREL_POWER_STANDBY:	0.70
EPREL_POWER_STANDBY_NETWORKED:	0.70
EPREL_R9_COLOUR_RENDERING_INDEX:	25
EPREL_REGISTRANT_NATURE:	MANUFACTURER
EPREL_STROBOSCOPIC_EFFECT_METRIC:	0.1
EPREL_SURVIVAL_FACTOR:	0.55
Grösse:	300*70
LED - Gehäusematerial:	Stahl
Lichtfarbe:	RGB-WW
Lichtfarbe in Kelvin:	2700~6500
Lumen:	2000
Schutzklasse:	IP68
Volt:	12/24
Gewicht:	1.5 Kg

Weitere Bilder





COMPATIBLE REMOTE SHEET



Zubehör

Art.-Nr.	Name
178057	Synergy 21 LED LoRa (433MHZ) Poolleuchte 15W RGB+CCT *Milight/Miboxer*
178058	Synergy 21 LED LoRa (433MHZ) Controller DMX über LoRa *Milight/Miboxer*
178059	Synergy 21 LED LoRa (433MHZ) Poolleuchte 27W RGB+CCT *Milight/Miboxer*
178060	Synergy 21 LED LoRa (433MHZ) Unterwasserleuchte 9W RGB+CCT *Milight/Miboxer*
178061	Synergy 21 LED LoRa (433MHZ) PAR56 Pool Light 27W RGB+CCT *Milight/Miboxer*
178062	Synergy 21 LED LoRa (433MHZ) Fernbedienung*Milight/Miboxer*
178154	Synergy 21 LED LoRa (433MHZ) Garten Lampe 25W RGB-WW mit Funk IP66 230V *Milight/Miboxer*