

TURNTABLE & ACKERMAN TRUCKS



i Information

**SUITABLE FOR
USE THROUGHOUT
INDUSTRY**



TP622C

- » Manufactured from fully welded tubular steel & angle section with an exterior grade plywood platform

- » **Turntable Trucks:** fitted with ball-bearing turntable assembly. Easily steered when loaded
- » **Ackerman Trucks:** steers from a central pivot, transmitted by adjustable track rods. No possibility of tipping whilst turning as the wheels are located underneath the corners at all times



TP602C

Description	Model
Friction Parking Brake - Can be fitted to all new trucks. Operated by a foot pedal at the rear of the platform	TP709A

Wire Mesh Superstructure

- » Suitable for turntable or ackerman trucks without sides & ends
- » Height: 915mm infilled with 50 x 50mm mesh
- » Box construction with 1 lift out long side

Platform Size mm	Box Suffix	Box with Half Drop Side Suffix
1200 x 700	/ WM	/ WG
1500 x 800	/ WM	/ WG
2000 x 1000	/ WM	/ WG

Load Capacity	Platform Size mm	Platform Height mm	Wheels 4 x Roller Bearing	Without Sides & Ends		With Sides & Ends (300mm Deep)	
				Weight	Plywood Model	Weight	Plywood Model
Turntable Trucks							
750 kg	1200 x 700	505	400mm Pneumatic	62 kg	TP600C	88 kg	TP620C
1000 kg	1500 x 800		400mm Cushion	105 kg	TP601M	133 kg	TP621M
			400mm Pneumatic	77 kg	TP601C	105 kg	TP621C
	2000 x 1000		400mm Cushion	132 kg	TP602M	165 kg	TP622M
			400mm Pneumatic	105 kg	TP602C	138 kg	TP622C
Two Wheel Ackerman Trucks							
1000 kg	1500 x 800	505	400mm Pneumatic	79 kg	TP603C	109 kg	TP623C
			400mm Cushion	106 kg	TP603M	137 kg	TP623M
	2000 x 1000		400mm Pneumatic	99 kg	TP604C	133 kg	TP624C
			400mm Cushion	126 kg	TP604M	160 kg	TP624M