



Datasheet for part number DBMMY9W4PA101

|   |
|---|
| Our Catalog Part Number: DBMMY-9W4P-A101                                  |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D |

| Product Datasheet               |   |
|---------------------------------|---|
| General                         | Combo D Series: D-Subminiature offering mixed layouts     |
| Wire Gauge Range AWG            | AWG 8-26  |
| Contact Arrangement             | 9W4 (5 contacts size 20, 4 empty size 8 cavities)         |
| Dielectric Withstanding Voltage | 500 VAC at sea level                                      |
| Current Rating Signal Contacts  | 7.5 max   |
| Operating Temperature           | -55°/+150°  |
| Salt Spray Test                 | 48 hours (96 Hrs for Stainless Steel)                     |
| Shell Material                  | Carbon Steel  |
| Shell Finish                    | Cadmium plating   |
| Insulator Material              | Thermoplastic, type PCT UL 94V-0                          |
| Insulator Color                 | black   |
| Gender                          | Pin   |
| Contacts                        | delivery without size 8 contacts, please order separately |
| Mounting Method                 | Dual Float Mount  |