
KANALFLEX FLEXIBLE CABLE TRUNKING

Overview

A flexible routing system made from grey polypropylene. The upper 'tongues' of the section are inclined downward to facilitate easy insertion of cables. Supplied with adhesive fixing strip and pre-drilled for additional screw fixing as required. Supplied in lengths of 500mm in packs of 10 lengths.



Part No	Reference	Dimensions mm	Pack Qty
B0905	BK1313A	12.5 X 12.5	10 X 0.5M
B0906	BK1616A	16 X 16	10 X 0.5M
B0907	BK2020A	20 X 20	10 X 0.5M
B0908	BK2525A	25 X 25	10 X 0.5M
B0909	BK3030A	30 X 30	10 X 0.5M
B0910	BK4040A	40 X 40	10 X 0.5M
B0911	BK5050A	50 X 50	10 X 0.5M

Features & Benefits

- RAL7040
- Operating temperature: continuous 80°C, short period 140°C
- Dielectric rigidity 25KV/mm
- Free of silicone, cadmium, lead, heavy metals and bromide additives.
- Polypropylene blended, self extinguishing UL94V2

For more information please visit www.hellermanntyton.co.uk

