

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192030389**
Status: **Active**
Overview: High-Temperature Temp Terms Terminals and Splices
Description: Krimptite Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification 194130096-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series 19203
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview High-Temperature Temp Terms Terminals and Splices
 Product Name Krimptite
 Type Ring
 UPC 822348424788

Physical

Barrel Type Closed
 Insulation None
 Material - Metal Steel
 Material - Plating Mating Nickel
 Net Weight 1.180/g
 Packaging Type Carton
 Stud Size 10 (M5)
 Temperature Range - Operating 483°C
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 5.70mm max.
 Wire Size AWG 10, 12
 Wire Size mm² 4.00-6.00

Material Info

Reference - Drawing Numbers

Product Specification 194130096-000, PS-19902-011-001,
 PS-19902-013-001
 Sales Drawing SD-19203-018



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/108/2014 (17 Dec
 2014)

**Halogen-Free
 Status**

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

19203 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand	<u>640030100</u>
Crimp Tool	
Crimp Head for the	<u>640070100</u>
AT-200 Pneumatic	
Hand Tool	