
## Shielded D-Sub Backshells DSZK Series


## **TECHNICAL SPECIFICATIONS**

Cable diameter: Locking screws:

Assembly screws: Cable outlet: Attenuation factor: Zinc, Ni-plated -40°C - 120°C Polycarbonate PC UL94 V-0 3.0 - 13.0 mm Long jackscrews with groove for indication of thread Taptite threadforming Side > 40 dB between 30 MHz and 1 GHz







TYPE	Α	в
DSZK9	37,7	35
DSZK15	46	35

## PART NUMBERING SYSTEM

DSZK15 - M3.0 - BULK
Series:
K = Kit package BULK = Bulk / 100 pcs

## FEATURES

- Available in sizes 9 and 15
- Minimise interference from electromagnetic and RF sources
- Non-static parts avoid ESD problems
- Accept round foil and braided cable types
- Approved according VDE 0871, FCC 20780 and 89/336/EU
- Printed logotype available upon request
- Long jackscrews with UNC 4-40 thread as standard, M2.5, M2.6 or M3.0 as option
- For custom designed solutions, please consult factory