

Product data sheet

Item No. 92.257.4000.9

Cable assembly GST18I5K1BS 15 40PB02

geis® Extension cable female - male; length: 4m; type GST18I5;
5-pole;250/400 V / 16 A; colour of coding: pastel blue with black
strain-relief; cable: H05VV-F 5G1,5, colour: black



Item No.	92.257.4000.9
EAN	4015573609822
Order Unit	10 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 2
Interlockable	Yes
Color of coding/ contact carrier	Pastel blue
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	5
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Cable type	H05VV-F
Cable colour	Black
Cable diameter	10.1 mm
Version of cable	Female - male

Type of cord set	Connecting cable
Version cable end 1	GST18i5 socket
Version cable end 2	GST18i5 plug

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	4 m
--------------	-----