

ToLEDo Retro Ball Dimmable

TOLEDO RT BALL V3 ST DIM 470LM 865 E27
0028599



Product features

- Perfect for decorative and general lighting applications and creates a warm ambience similar to traditional lamps• The versatile ToLEDo Retro ball range is the ideal replacement for halogen and incandescent lamps and perfect for chandeliers and decorative applications• Same look, size and functionality as incandescent lamps• Omni-directional light distribution• A++ energy rating• Gives same sparkling light effect as the incandescent lamp• Dimensionally identical to incandescent lamps - fits all fixtures• Environment-friendly - no mercury and lower CO2 emissions• Dimmable with approved dimmers



PRODUCT OVERVIEW

Product name	TOLEDO RT BALL V3 ST DIM 470LM 865 E27
Technology	LED
Watt (Rated) (W)	4.5
Cap/Base	E27
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740890
Warranty	3 years
Luminous flux (lm)	470
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Wattage (W)	4.5
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288285993

DATA TABLE

General data

Product name	TOLEDO RT BALL V3 ST DIM 470LM 865 E27
Technology	LED
Watt (Rated) (W)	4.5
Cap/Base	E27
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740890
Warranty	3 years

Optical data

ToLEDo Retro Ball Dimmable

TOLEDO RT BALL V3 ST DIM 470LM 865 E27

0028599

Luminous flux (lm)	470
Luminous flux (Rated) (lm)	470
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	4.5
Equivalent watt (W)	40
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.75
No. Of switching cycles before premature failures	>50000
Inrush Current (A)	1.2
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	38
Max. Luminaires per 16A C Breaker	62
Max. Luminaires per 20A C Breaker	77

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	78
Nominal Product Diameter (mm)	45
Weight (kg)	0.045

Packaging

Single packaging type	Carton
Product EAN number	5410288285993
Packaging single length / height (cm)	5.0
Packaging single width (cm)	5.0
Packaging single depth (cm)	9.5
DUN14 (outer)	15410288285990
Units per outer package	6
Packaging outer length / height (cm)	15.8
Packaging outer width (cm)	10.7
Packaging outer depth (cm)	10.5

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes



ToLEDo Retro Ball Dimmable
TOLEDO RT BALL V3 ST DIM 470LM 865 E27
0028599

Safety message
Safety message

Not Suitable for totally enclosed fixtures
Dimmable with approved dimmers