

Mini Continuum II - Direct - Suspended Kit

MC2-KIT 2.4M 3K DALI WHT PRIS

2093153



Product features

- 2093153 MC2-KIT 2.4M 3K DALI WHT PRIS Continuous lines of LED light, white RAL 9016, direct distribution, suspended kit version is pre-wired and supplied complete with end caps and suspension cables, compact and minimalist design based on the Golden Mean, ideal for offices, meeting rooms, corridors, education facilities, museums and libraries, extruded aluminium body, diffuser: micro prismatic, colour temperature: 3000K warm white, total system power: 42W, total fixture output: 4200lm, luminaire efficacy: 100lm/W, LOR: 100%, colour rendering: Ra >80, LED Chromacity: 3 step MacAdam ellipse, lifespan: 66,000 hours L90B10, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 800mA, electronic driver, DALI dimmable, electrical protection: CLASS I, IP20, suitable for internal environment only.



PRODUCT OVERVIEW

Product name	MC2-KIT 2.4M 3K DALI WHT PRIS
Technology	LED
Housing	Aluminium
Mount	Suspended
Environment	Internal
General application	Education, Hospitality, Office, Retail
ETIM Class	EC001743
E-number FI	4237835
Warranty	5 years
Fixture luminous flux (lm)	4200
Luminaire efficacy (lm/W)	100
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 21
Photobiological Risk Group	RG0
Total power consumption (W)	42
Electrical protection	Class I
Control gear type	Electronic ballast
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768931538

DATA TABLE

Mini Continuum II - Direct - Suspended Kit

MC2-KIT 2.4M 3K DALI WHT PRIS

2093153

General data

Product name	MC2-KIT 2.4M 3K DALI WHT PRIS
Technology	LED
Housing	Aluminium
Mount	Suspended
Environment	Internal
General application	Education, Hospitality, Office, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001743
E-number FI	4237835
Warranty	5 years

Optical data

Fixture luminous flux (lm)	4200
Luminaire efficacy (lm/W)	100
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Glare control	< 21
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	42
Mains voltage (V)	220-240V
Lamp power factor	0.98
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	800
Inrush Current (A)	40
Inrush Duration (µs)	178
Energy Efficiency Class (A->G) of contained light source	C
Max. Luminaires per 10A C Breaker	15
Max. Luminaires per 13A C Breaker	20
Max. Luminaires per 16A C Breaker	23
Max. Luminaires per 20A C Breaker	30
Max. Luminaires per 10A B Breaker	9
Max. Luminaires per 13A B Breaker	12
Max. Luminaires per 16A B Breaker	14
Max. Luminaires per 20A B Breaker	18

Lifetime data

Lifespan L70 B50	120000
-------------------------	--------

Mini Continuum II - Direct - Suspended Kit MC2-KIT 2.4M 3K DALI WHT PRIS 2093153

Lifespan L80 B20	120000
Lifespan L90 B10	66000


Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser finish	Prismatic
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	2400
Nominal Product Width (mm)	54
Nominal Product Height (mm)	86
Weight (kg)	6.3


Packaging

Single packaging type	Carton
Product EAN number	5025768931538
Packaging single length / height (cm)	254.0
Packaging single width (cm)	15.0
Packaging single depth (cm)	15.0
DUN14 (outer)	05025768931538
Units per outer package	1
Packaging outer length / height (cm)	254.0
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	15.0

PHOTOMETRY



Mini Continuum II - Direct - Suspended Kit MC2-KIT 2.4M 3K DALI WHT PRIS 2093153



TECHNICAL DRAWINGS

