

## Boring bar holder, shape E2

For turning tools with cylindrical shanks

**ORION**<sup>®</sup>

### Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm<sup>2</sup>
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground
- Internal and external coolant supply

<b>Art. no.</b>	<b>22778 130</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22778130
<b>VDI mount diameter</b>	50 mm
<b>Clamping diameter</b>	50 mm
<b>Length</b>	30 mm
<b>Outer diameter</b>	98 mm
<b>Projecting length</b>	100 mm
<b>Gross Weight</b>	5.600 kg
<b>Product Group</b>	2AC



### EAN

4053625465286

