

Universal external and internal extractor set

Max. 170 mm clamping width and max. 250 mm clamping depth



Application:

For internal and external extraction with a range of clamping depths.

Execution:

- Forged traverses and pull-out hooks
- One 2- and one 3-arm traverse, 2 spindles and 3 narrow pull-out hooks in each of 3 lengths 100/200/250 mm. Clamping depths up to 250 mm. Maximum external clamping width 130 mm, internal 170 mm. Delivery in case with foam insert

Art. no.	55026 090
Brand	GEDORE
Manufacturer Part Number	8117340
Min./max. clamping width	80-170 mm
Min./max. clamping depth	50-250 mm
Max. clamping depth	250 mm
Min. clamping depth	50 mm
Max. clamping width	170 mm
Min. clamping width	80 mm
Gross Weight	6.400 kg
Product Group	5JB



EAN

4036976104134