

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



## Technical Datasheet

# tasker® RG 213U MIL. C17F Standards - Coaxial Cable 50 Ω




**CATEGORY** Coaxial cable 50 Ω (See tasker Video Catalogue)

- A:** Black PVC Sheath. Outer Diam. Ø 10,40 (±0,20) mm.
- B:** Shielding in O.F.C. red copper braid covering 98% .
- C:** Core Insulation with compact PE – Diam.. Ø 7,30 (±0,20) mm.
- D:** Stranded O.F.C. red copper formation 7x0,75 mm.  
Nom. Cross section 1x3,09 mm<sup>2</sup>.

**MARKING  
CUSTOM**

**tasker®** RG 213 U MIL - C-17 50 OHM Made in Italy  
 This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

### Impedance Test from 50MHz to 1,0 GHz



### Cable Properties

<b>Conductor Resistance</b>	6 Ω/Km ± 5%
<b>Capacity Core/Shield</b>	100 pF/mt
<b>Velocity of Propagation</b>	66%
<b>Impedance</b>	50 Ω ± 3%
<b>Max Rated Voltage</b>	5.000 V
<b>Operative Temperature</b>	-15/+70 °C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 27.06.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			