



Part no.: 50114696
KB DN/CAN-5000 BA
Connection cable




Figure can vary

Contents

- Technical data
- Electrical connection

Part no.: 50114696 – KB DN/CAN-5000 BA – Connection cable

Technical data

Basic data

Suitable for interface	CANopen DeviceNet
------------------------	----------------------

Connection

Connection 1

Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Connection 2

Type of connection	Open end
--------------------	----------

Cable properties

Number of conductors	5 Piece(s)
Sheathing color	Black
Shielded	Yes
Cable design	Connection cable (open on one end)
Cable diameter (external)	7 mm
Cable length	5,000 mm
Sheathing material	PUR
Suitability for drag chains	Yes
Traverse rate	Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 5m/s ²

Mechanical data

Classification


Customs tariff number	85444290
eCl@ss 8.0	27279218
eCl@ss 9.0	27060311
ETIM 5.0	EC001855
ETIM 6.0	EC001855

Electrical connection

Connection 1	
Type of connection	Connector
Thread size	M12
Type	Female
No. of pins	5 -pin
Encoding	A-coded
Design	Axial

Part no.: 50114696 – KB DN/CAN-5000 BA – Connection cable

Pin	Conductor color
1	Drain wire
2	Red
3	Black
4	White
5	Blue



Connection 2	
Type of connection	Open end