



Part no.: 50130942
KDS U-M12-4W-M12-4A-P1-010-3DP
Interconnection cable




Figure can vary

Contents

- Technical data
- Electrical connection

Technical data

Connection

Connection 1

| | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Female |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Design | Angled |
| Connector, LED | Yes |

Connection 2

| | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Male |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Design | Axial |

Cable properties

| | |
|-----------------------------------|---|
| Number of conductors | 4 Piece(s) |
| Wire cross section | 0.34 mm ² |
| AWG | 22 |
| Sheathing color | Black |
| Shielded | No |
| Silicone-free | Yes |
| Cable design | Interconnection cable |
| Cable diameter (external) | 4.7 mm |
| Cable length | 1,000 mm |
| Sheathing material | PUR |
| Wire insulation | PP |
| Traverse rate | Max. 3.3 m/s with horiz. traverse path of 5m and and max. acceleration of 5m/s ² |
| Suitability for drag chains | Yes |
| Properties of the outer sheathing | Free of CFC, cadmium, silicone, halogen and lead, matt, low-adhesion, abrasion-resistant, easily machine-processable |
| Resistance of the outer sheathing | Hydrolysis and microbe resistant, good oil, gasoline and chemical resistance in accordance with VDE 0472 part 803 test B, flame retardant in accordance with UL 1581 VW1 / CSA FT1 / IEC 60332-1, IEC 60332-2-2 |
| Torsion suitability | ±180° / m (max. 2 mio. cycles with 35 cycles / min) |

Mechanical data

| | |
|---|--------------------------|
| Width across flats | 13 mm |
| Bending cycles | 5,000,000 Piece(s) |
| Bending radius, flexible laying, min. | Min. 10 x cable diameter |
| Bending radius, stationary laying, min. | Min. 5 x cable diameter |

Operation and display

| | |
|----------------|------------|
| Number of LEDs | 3 Piece(s) |
|----------------|------------|

Environmental data

| | |
|--|---------------|
| Ambient temperature, operation, flexible use | -25 ... 80 °C |
|--|---------------|

Part no.: 50130942 – KDS U-M12-4W-M12-4A-P1-010-3DP – Interconnection

| | |
|--|---------------|
| Ambient temperature, operation, stationary use | -40 ... 80 °C |
|--|---------------|

Certifications


| | |
|----------------------|----------------|
| Degree of protection | IP 65 IP 67 |
| Certifications | c UL US |

Classification

| | |
|-----------------------|----------|
| Customs tariff number | 85444290 |
| eCl@ss 8.0 | 27279218 |
| eCl@ss 9.0 | 27060311 |
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |

Electrical connection

| Connection 1 | |
|--------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Female |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Design | Angled |
| Connector, LED | Yes |



| Connection 2 | |
|----------------------|-----------|
| Type of connection | Connector |
| Thread size | M12 |
| Type | Male |
| Handle body material | |
| No. of pins | 4 -pin |
| Encoding | A-coded |
| Design | Axial |
| Lock | |

