

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	AJS9
Product ID:	1SNA179726R0200
EAN:	3472591797268
Catalog Description:	AJS9 Test Sockets Yellow
Long Description:	- Insulated test sockets, - Many colors available for circuit identification, - Compatible with standard DIA 4 mm 0.157 in test plugs: - insulated (according to IEC 60101-031) - not insulated (with mobile protection), - Compatible with ZS10-ST...SNK series terminal blocks, M6/8.ST...SNA series terminal blocks, D6/8.ST.RS..Solution series terminal blocks

Ordering

Color:	Yellow
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	6.3 mm
Product Net Height:	6.3 mm
Product Net Depth / Length:	33.6 mm
Product Net Weight:	3.6 g

Technical

Spacing:	4 mm
Function:	Test Sockets
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	D6/8.ST.RS M6/8.ST ZS10-PE-R1 ZS10-R1 ZS10-ST

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Classifications

Object Classification Code: X

Container Information

Package Level 1 Units: 25 piece

Package Level 1 Width: 125 mm

Package Level 1 Depth / Length: 170 mm

Package Level 1 Height: 5 mm

Package Level 1 Gross Weight: 0.09 kg

Package Level 1 EAN: 3472591797268

Package Level 2 Units: 1000 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 500 mm

Package Level 2 Height: 150 mm

Package Level 3 Units: 48000 piece

Product Packing Type: Bag

