

Lösbare Doppelgewindenippel



Gewinde 1	Gewinde 2	SW 1	SW 2	Messing	Messing vernickelt	Edelstahl 1.4571	Edelstahl 1.4408
R 1/8	R 1/8	15 mm	5 mm	MS252L1818	MSN252L1818	-	-
R 1/8	R 1/4	15 mm	5 mm	MS252L1814	MSN252L1814	-	-
R 1/4	R 1/4	19 mm	6 mm	MS252L1414	MSN252L1414	-	-
R 1/4	R 3/8	19 mm	6 mm	MS252L1438	MSN252L1438	-	-
R 3/8	R 3/8	22 mm	8 mm	MS252L3838	MSN252L3838	-	-
R 1/2	R 1/2	27 mm	12 mm	MS252L1212	MSN252L1212	-	-
R 3/4	R 3/4	36 mm	14 mm	MS252L3434	MSN252L3434	-	-
R 1	R 1	50 mm	19 mm	MS252L11	MSN252L11	-	-
R 1 1/4	R 1 1/4	60 mm	22 mm	MS252L114114	MSN252L114114	-	-
R 1 1/2	R 1 1/2	70 mm	24 mm	MS252L112112	MSN252L112112	-	-
R 2	R 2	80 mm	32 mm	MS252L22	MSN252L22	-	-

Doppelgewindenippel, Außengewinde zylindrisch



Gewinde	Gewinde	SW	Messing	Messing vernickelt	Edelstahl 1.4571	Edelstahl 1.4408
M3	M3	5 mm	MS252M33	MSN252M33	-	-
M5	M3	7 mm	MS252M53	MSN252M52	-	-
M14x1,5	M14x1,5	17 mm	MS252M1414	MSN252M1414	-	-
M16x1,5	M16x1,5	19 mm	MS252M1616	MSN252M1616	-	-
M24x1,5	M24x1,5	28 mm	MS252M2424	MSN252M2424	-	-
M5	M5	7 mm	MS252M55	MSN252M55	252 C-ES	-
M5	G 1/8	14 mm	MS252M518	MSN252M518	252 D-ES	-
M5	G 1/4	17 mm	MS252M514	MSN252M514	252 E-ES	-
G 1/4	M14x1,5	17 mm	MS25214M14	MSN25214M14	-	-
G 3/8	M16x1,5	19 mm	MS25238M16	MSN25238M16	-	-
G 1/2	M24x1,5	28 mm	MS25212M24	MSN25212M24	-	-
G 1/8	G 1/8	14 mm	MS2521818	MSN2521818	252 A-ES	DGNG18ES4408
G 1/8	G 1/4	17 mm	MS2521814	MSN2521814	252 B-ES	-
G 1/8	G 3/8	19 mm	MS2521838	MSN2521838	252 B/1-ES	-
G 1/4	G 1/4	17 mm	MS2521414	MSN2521414	252.01-ES	DGNG14ES4408
G 1/4	G 3/8	19 mm	MS2521438	MSN2521438	252.02-ES	-
G 1/4	G 1/2	24 mm	MS2521412	MSN2521412	252.02/S-ES	-
G 1/4 links	G 1/4 links	17 mm	MS252LH1414	-	-	-
G 3/8 links	G 3/8 links	19 mm	MS252LH3838	-	-	-
G 3/8	G 3/8	19 mm	MS2523838	MSN2523838	252.03-ES	DGNG38ES4408
G 3/8	G 1/2	24 mm	MS2523812	MSN2523812	252.04-ES	-
G 3/8	G 3/4	32 mm	MS2523834	MSN2523834	252.04/S-ES	-
G 3/8	G 1	38 mm	MS252381	MSN252381	-	-
G 1/2	G 1/2	24 mm	MS2521212	MSN2521212	252.04-ES	DGNG12ES4408
G 1/2	G 3/4	32 mm	MS2521234	MSN2521234	-	-
G 1/2	G 1	38 mm	MS252121	MSN252121	252.06/S-ES	-
G 3/4	G 3/4	32 mm	MS2523434	MSN2523434	252.07-ES	DGNG34ES4408
G 3/4	G 1	38 mm	MS252341	MSN252341	252.07/1-ES	-
G 1	G 1	38 mm	MS25211	MSN25211	252.07/2-ES	DGNG1ES4408
G 1	G 1 1/4	50 mm	MS2521114	MSN2521114	-	-
G 1	G 1 1/2	55 mm	MS2521112	MSN2521112	-	-
G 1	G 2	70 mm	MS25212	MSN25212	-	-
G 1 1/4	G 3/4	50 mm	MS25211434	MSN25211434	-	-
G 1 1/4	G 2	70 mm	MS2521142	MSN2521142	-	-
G 1 1/4	G 1/2	50 mm	MS25211412	MSN25211412	-	-
G 1 1/4	G 1 1/4	50 mm	MS252114114	MSN252114114	-	DGNG114ES4408
G 1 1/4	G 1 1/2	55 mm	MS252114112	MSN252114112	-	-
G 1 1/2	G 3/4	50 mm	MS25211234	MSN25211234	-	DGNG112ES4408
G 1 1/2	G 1 1/2	55 mm	MS252112112	MSN252112112	-	-
G 1 1/2	G 2	70 mm	MS2521122	MSN2521122	-	-
G 2	G 3	95 mm	MS25223	MSN25223	-	-

G 2	G 2	70 mm	MS25222	MSN25222	-	DGNG2ES4408
G 2	G 2 1/2	80 mm	MS2522212	MSN2522212	-	-
G 2 1/2	G 2 1/2	80 mm	MS252212212	MSN252212212	-	-
G 2 1/2	G 3	95 mm	MS2522123	MSN2522123	-	-
G 3	G 3	95 mm	MS25233	MSN25233	-	-

Doppelgewindenippel, Außengewinde konisch



Gewinde	Gewinde	SW	Messing	Messing vernickelt	Edelstahl 1.4571	Edelstahl 1.4408
R 1/8	R 1/8	12 mm	MS252R1818	MSN252R1818	252.400-ES	DGNR18ES4408
R 1/8	R 1/4	14 mm	MS252R1814	MSN252R1814	252.400/2-ES	-
R 1/8	R 3/8	19 mm	MS252R1838	MSN252R1838	252.400/3-ES	-
R 1/4	R 1/4	14 mm	MS252R1414	MSN252R1414	252.301-ES	DGNR14ES4408
R 1/4	R 3/8	19 mm	MS252R1438	MSN252R1438	252.401/2-ES	-
R 1/4	R 1/2	22 mm	MS252R1412	MSN252R1412	252.401/4-ES	-
R 3/8	R 3/8	19 mm	MS252R3838	MSN252R3838	252.302-ES	DGNR38ES4408
R 3/8	R 1/2	22 mm	MS252R3812	MSN252R3812	252.402/2-ES	-
R 3/8	R 3/4	28 mm	MS252R3834	MSN252R3834	-	-
R 3/8	R 1	36 mm	MS252R381	MSN252R381	252.402/4-ES	-
R 1/2	R 1/2	22 mm	MS252R1212	MSN252R1212	252.303-ES	DGNR12ES4408
R 1/2	R 3/4	28 mm	MS252R1234	MSN252R1234	252.403/2-ES	-
R 1/2	R 1	36 mm	MS252R121	MSN252R121	252.403/3-ES	-
R 3/4	R 3/4	28 mm	MS252R3434	MSN252R3434	252.304-ES	DGNR34ES4408
R 3/4	R 1	36 mm	MS252R341	MSN252R341	252.404/2-ES	-
R 1	R 1	36 mm	MS252R11	MSN252R11	252.305-ES	DGNR1ES4408
R 1	R 1 1/4	44 mm	MS252R1114	MSN252R1114	252.405/2-ES	-
R 1	R 1 1/2	50 mm	MS252R1112	MSN252R1112	252.405/3-ES	-
R 1	R 2	62 mm	MS252R12	MSN252R12	252.405/4-ES	-
R 1 1/4	R 1/2	44 mm	MS252R11412	MSN252R11412	252.406/2-ES	-
R 1 1/4	R 3/4	44 mm	MS252R11434	MSN252R11434	-	-
R 1 1/4	R 1 1/4	44 mm	MS252R114114	MSN252R114114	252.406-ES	DGNR114ES4408
R 1 1/4	R 1 1/2	50 mm	MS252R114112	MSN252R114112	252.407-ES	-
R 1 1/4	R 2	62 mm	MS252R1142	MSN252R1142	252.406/3-ES	-
R 1 1/2	R 3/4	50 mm	MS252R11234	MSN252R11234	-	-
R 1 1/2	R 1 1/2	50 mm	MS252R112112	MSN252R112112	-	DGNR112ES4408
R 1 1/2	R 2	62 mm	MS252R1122	MSN252R1122	252.407/2-ES	-
R 2	R 2	62 mm	MS252R22	MSN252R22	252.408-ES	DGNR2ES4408
R 2	R 2 1/2	78 mm	-	-	252.408/2-ES	-
R 2	R 3	90 mm	-	-	252.408/3-ES	-
R 2 1/2	R 2 1/2	78 mm	-	-	252.409-ES	DGNR212ES4408
R 2 1/2	R 3	90 mm	-	-	252.409/2-ES	-
R 3	R 3	90 mm	-	-	252.410-ES	DGNR3ES4408