

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **1200652308**
Status: **Active**
Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Description: Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, Female (Straight) to Pigtail, 24 AWG, Unshielded WSOR Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series 120065
 Connector End A Micro-Change (M12)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Brass
 Overview Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
 Product Name Micro-Change (M12)
 Region Europe
 Type Single Ended
 UPC 889056029490

Physical

Cable Diameter 6.40mm (.252")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Black
 Coupling Style Knurled Hexnut, Threaded
 Gender Female-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket TPU
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - Plating Mating Gold
 Orientation Straight to Pigtail
 Poles 8
 Temperature Range - Operating -25°C to +85°C
 Wire Size AWG 24
 Wire/Cable Type WSOR

Electrical

Current - Maximum per Contact 2.0A
 Voltage - Maximum 30V

Material Info

Engineering Number 808000B41M050



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

120065 Series