

## Myriad Deco IP65 White Bezel


MYRIAD DECO IP65 SPOT 4000K PHDM EM WHITE WBEZ

2058866



### Product features

- MYRIAD IP65 SPOT 4000K Phase dimmable with white reflector, white bezel and 3 hour emergency.



### PRODUCT OVERVIEW

Product name	MYRIAD DECO IP65 SPOT 4000K PHDM EM WHITE WBEZ
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	1132
Luminaire efficacy (lm/W)	94
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	28
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	344
Luminous flux (emergency) (lm)	344
Total power consumption (W)	12
Electrical protection	Class II
Control gear type	Electronic ballast
Dimming method	Other
Minimum dimming level (%)	10
Housing colour	White
IP rating	IP65/20
IK rating	IK02
Product EAN number	5025768588664

### DATA TABLE

## Myriad Deco IP65 White Bezel

MYRIAD DECO IP65 SPOT 4000K PHDM EM WHITE WBEZ

2058866

### General data

Product name	MYRIAD DECO IP65 SPOT 4000K PHDM EM WHITE WBEZ
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	1132
Luminaire efficacy (lm/W)	94
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	28
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	344
Luminous flux (emergency) (lm)	344
Emergency duration (h)	3

### Electrical data

Total power consumption (W)	12
Mains voltage (V)	230-240V
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	Other
Minimum dimming level (%)	10
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

### Physical data

Housing colour	White
IP rating	IP65/20
IK rating	IK02

## Myriad Deco IP65 White Bezel





MYRIAD DECO IP65 SPOT 4000K PHDM EM WHITE WBEZ  
2058866

Diffuser finish	Bezel (or Ring)
Nominal Product Height (mm)	72
Nominal Product Diameter (mm)	90
Cutout Dimensions (W x L in mm or Diameter in mm)	76
Weight (kg)	1.44
Recessed Depth (mm)	72

### Packaging

Single packaging type	Carton
Product EAN number	5025768588664
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768588664
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

## PHOTOMETRY




## Myriad Deco IP65 White Bezel

*MYRIAD DECO IP65 SPOT 4000K PHDM EM WHITE WBEZ*

2058866

### TECHNICAL DRAWINGS

---



Dimensions (mm)