

## Myriad Pendant White - Surface Mounted

MYRIAD PENDANT 3000K SURFACE MTD SWITCHED WHITE  
2050679



### Product features

- High-end architectural (3000K) warm white LED pendant with non dimmable driver and surface mounted housing, finished in a white finish (RAL9016)



### PRODUCT OVERVIEW

Product name	MYRIAD PENDANT 3000K SURFACE MTD SWITCHED WHITE
Technology	LED
Mount	Ceiling surface mounting
Environment	Indoor
General application	Hospitality, Office, Retail, Residential & Consumer
ETIM Class	EC001743
E-number FI	4275458
E-number SE	7561416
E-number Norway	3290202
Warranty	5 years
Fixture luminous flux (lm)	1114
Luminaire efficacy (lm/W)	111.4
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Beam Angle (°)	30
Total power consumption (W)	10
Electrical protection	Class II
Control gear mounting	Integral
Dimmable	No
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768506798

## Myriad Pendant White - Surface Mounted

*MYRIAD PENDANT 3000K SURFACE MTD SWITCHED WHITE*  
2050679

### DATA TABLE

#### General data

<b>Product name</b>	MYRIAD PENDANT 3000K SURFACE MTD SWITCHED WHITE
<b>Technology</b>	LED
<b>Mount</b>	Ceiling surface mounting
<b>Environment</b>	Indoor
<b>General application</b>	Hospitality, Office, Retail, Residential & Consumer
<b>Performance ambient temperature Tq (°C)</b>	25
<b>ETIM Class</b>	EC001743
<b>E-number FI</b>	4275458
<b>E-number SE</b>	7561416
<b>E-number Norway</b>	3290202
<b>Warranty</b>	5 years

#### Optical data

<b>Fixture luminous flux (lm)</b>	1114
<b>Luminaire efficacy (lm/W)</b>	111.4
<b>LOR (%)</b>	100
<b>Colour temperature (K)</b>	3000
<b>Light colour</b>	Warm White
<b>CRI (Ra)</b>	80
<b>Adjustable chromaticity</b>	N
<b>Beam Angle (°)</b>	30
<b>Distribution type</b>	Symmetric

#### Electrical data

<b>Total power consumption (W)</b>	10
<b>Mains voltage (V)</b>	220-240V
<b>Electrical protection</b>	Class II
<b>Control gear mounting</b>	Integral
<b>Transformer required</b>	Yes
<b>Dimmable</b>	No
<b>Dimming method</b>	N/A
<b>Drive current (mA)</b>	250
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	D
<b>Nominal Frequency (Hz)</b>	50/60Hz

#### Lifetime data

<b>Lifespan L70 B50</b>	50000
-------------------------	-------

#### Physical data

<b>Housing colour</b>	White
<b>IP rating</b>	IP20
<b>IK rating</b>	IK02
<b>Nominal Product Length (mm)</b>	75
<b>Nominal Product Width (mm)</b>	75

## Myriad Pendant White - Surface Mounted



*MYRIAD PENDANT 3000K SURFACE MTD SWITCHED WHITE*  
2050679

Nominal Product Height (mm)	129
Nominal Product Diameter (mm)	75
Max. Lamp Diameter (mm) - D	75
Weight (kg)	0.95

### Packaging

Single packaging type	Carton
Product EAN number	5025768506798
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

### PHOTOMETRY



### TECHNICAL DRAWINGS

