



Standard lamps
Dental technology


For special features, specific benefits and areas of use see page 104



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D mm	Total length L max. mm	Light centre length mm	Luminous flux lm	Average life h	Individual life h	Burning position	PU
00936041	24V 40W BX22d transversal	24	40		BX22d	50	86		550	600			
00936009	24V 50W BX22d transversal	24	50		BX22d	50	82		670	300			
00936046	50V 50W BX22d transversal	50	50		BX22d	50	82		415	1,000			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter D mm	Total length L max. mm	Light centre length mm	Luminous flux lm	Average life h	Individual life h	Burning position	PU
00936023	24V 25W BA20d transversal	24	25		BA20d	40	64		350	500			
00936042	24V 25W BA20d transversal	24	25		BA20d	40	max. 68		330	600			
00936016	24V 60W BA20d axial	24	60	2.5	BA20d	40	max. 68		860	400			



Article no.	Description	V	W	Am- perage	Cap	Bulb diameter mm	Total length max. mm	Light centre length mm	Luminous flux lm	Average life h	Individual life h	Burning position	PU
00936026	24V 75/75W E27	24	75/75		E27	80	150	110	1,700	100			
00936025	24V 100/100W E27	24	100/100		E27	90	170	130	3,500	100			
00936033	24V 50/50W B22d/25x26	24	50/50		B22d	70	117	78	1,400	300			