

LogiLink®

Alumium Monitor Desk Mount with Gas Spring for 13"-32" Flat & Curved Monitor


Art. No.: BP0042



Easy installation and compatible with VESA standard max. 100x100mm.

Features:

- » Super strong mounting brackets: Solid-reinforced Cold Steel, durable product with maximum capacity of 9kg
- » Maximum arm extension length is 525mm, Tilt capacity: 90°~-90°, Swivel capacity: 90°~-90° and Rotation capacity: 90°~-90°
- » Compatible with VESA 75x75mm, 100x100mm
- » Gas spring offers adjustable counterbalance to the direction of the monitor
- » Built-in spring gauge can adjust various monitor weights
- » Easy cable management inside the adjustable arms
- » Easy to install and height adjustable
- » Clamp and grommet mount included
- » Fit for 13-32 inch LCD Monitor



* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered namework of their respective owners.



BP0042



4 052792 046472

Made in China

Best Connectivity


LogiLink®

Alumium Monitor Desk Mount with Gas Spring for 13"-32" Flat & Curved Monitor


Art. No.: BP0042




1




2



3



4



Specification:

Screen Size	13"-32"
Rated Load	1-9kg/2.2-19.8lbs
VESA	75x75, 100x100
Arm Extend	525mm
Tilt	90° ~ -90°
Swivel	90° ~ -90°
Rotate	90° ~ -90°
Product Size	115 x 590 x 665mm

Fits
13"-32"
Monitor

VESA
Max.
100x100mm

Arm
Extend
525mm

rated
1-9kg/
2.2-19.8lbs

Gas
Spring
Arm

90°
-90° 90°
ROTATION

90°
-90°
TILT

90°
-90°
SWIVEL

↑
Direction
Indicator

Curved
Monitor

Package Contents:

- » 1 x Alumium Monitor Desk Mount
- » 1 x Screw Package
- » 1 x User Manual

Package Informations:

- » Packing Dimension: mm
- » Packing Weight: kg
- » Carton Dimension: mm
- » Carton Q'ty: pcs
- » Carton Weight: kg

ROHS
compliant

* The specifications and pictures are subject to change without notice.
* All trade names referenced are the registered namework of their respective owners.



BP0042



4 052792 046472

Made in China

Best Connectivity