



Inspection lights

High performance COB-LED with additional torch light.
4 Lighting modes: standard, red, torch, tip.

1. Battery life indicator.
2. Charge time: 4hrs.
3. Integrated rechargeable 3.7V 2600mAh Li-Ion battery.
4. Integrated magnet.
5. Clamp and hanging hook.



Inspection Lights



C.K. MINI LED Inspection Light

Compact Inspection light with dual function LED. Lightweight pocket friendly design with clip. Tactile on/off mode switch. CKlearView LED for accurate colour rendering. 120lm main light. 80lm torch light. 3.7V 750mAh Li-ion battery for up to 4.5 hours runtime. USB-C rechargeable in 1.5 hours (cable included).

Item No.	i	📦
T9426USB	150lm	5



C.K. MIDI LED Inspection Light

High powered Inspection light with dual function LED. IK07 moulded design for exceptional durability. Tactile on/off mode switch. CKlearView LED for accurate colour rendering. 400lm main light with eco mode (250lm). 100lm torch light. Flexible 180° folding design with magnetic base. Retractable 360° rotating hook. IP54 rated against dust and water ingress. 3.7V 2600mAh Li-ion battery for up to 5.0 hours runtime. Battery level indicator. USB-C rechargeable in 3.5 hours (cable included).

Item No.	i	📦
T9427USB	400lm	8



C.K. MAXI LED Inspection Light

High Powered Inspection light with dual function LED. IK07 moulded design for exceptional durability. Tactile on/off mode switch. CKlearView LED for accurate colour rendering. 700lm dimmable main light with eco mode (175lm). 150lm torch light. Flexible 180° folding design with magnetic base. Retractable 360° rotating hook. IP65 rated against dust and water ingress. 3.7V 2600mAh Li-ion battery for up to 8.0 hours runtime. Battery level indicator. USB-C rechargeable in 3.5 hours (cable included).

Item No.	i	📦
T9428USB	700lm	5